

## Model 430 – raising the bar for compact Ozone Analyzers.



Teledyne API is pleased to offer the Model 430 Compact O<sub>3</sub> Analyzer. The Model 430 uses the proven UV Absorption principle, producing accurate and stable O<sub>3</sub> measurements. The robust design and low power consumption makes it ideal for monitoring applications that require long autonomy periods such as rural and remote monitoring, saturation studies, and atmospheric research. The small footprint and quiet operation make it extremely useful for indoor air quality, surveying, and industrial hygiene applications. An optional battery pack provides up to 14 hrs. of run time on a full charge.







## Model 430 Specifications

Ranges	0 - 100 ppb (min), 0 - 20,000 ppb (max) (user-selectable
Measurement Units	ppb, ppm (user-selectable)
Zero Noise	< 1 ppb (RMS)
Span Noise	< 0.5% of reading (RMS) above 100 ppb
Lower Detectable Limit	< 2 ppb
Zero Drift	< 1 ppb/24 hours
Span Drift	< 1% full-scale/24 hours
Lag Time	< 20s
Rise/Fall Time	< 15s to 95%
Linearity	1% full-scale
Precision	< 0.5 ppb or 0.5% of reading above 100 ppb
Sample Flow Rate	0.8 L/min +/-10%
Typical Power Consumption	12VDC, 9W
Analog Output Ranges	0 - 5V
Analog Output Resolution	16-Bit Resolution
Internal Data Storage Capacity	10,000 lines (1 hr avg = 1.1 yr)
Included I/O	1X RS-232 1X 0-5V analog output 5X 0-5V analog input 1X SD card slot
Dimensions H x W x D	4.2" x 7.1" x 10.2" (107 x 180 x 259 mm)
Weight	5.2 lbs (2.4 kg)
Operating Temperature Range	5 - 40°C (with US EPA approval)
Humidity Range	0 - 95% RH non-condensing
Certifications	US EPA Federal Equivalent Method EQOA-1015-229

Specifications subject to change without notice. All specifications are based on constant conditions.



9970 Carroll Canyon Road 
San Diego, CA 92131
Ph. 858-657-9800
Fax 858-657-9816
Email api-sales@teledyne.com

For more information about the Teledyne API family of monitoring instrumentation products, call us or visit our website at:

## www.teledyne-api.com

© 2018 Teledyne API Printed documents are uncontrolled. SAL000089F (DCN 7833) 02.09.18

